

Exh C - Att: 3

CLARIFICATION LIST OF LOGIC BURN-IN PARTS FROM DN-41, DATED JUNE 30, 1999

PHILIPS PART NUMBER	PHILIPS PKG	PHILIPS PART DESCRIPTION	PHILIPS 12 NC NUMBER	LAST TIME BUY DATE	LAST TIME DLVY DATE	REPLACEMENT PART	STATUS CODE(S)	COMMENTS
74HC00	N-B	BURN-IN VERSION	933776750652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume, limited mfg capability
74HC00D/S15	D	Selection Type only	935073690118	12/31/99	06/30/00	Standard product	7	No Volume
74HC02	N-B	BURN-IN VERSION	933795410652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC08	N-B	BURN-IN VERSION	933795430652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC125	N-B	BURN-IN VERSION	933795500652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC132	N-B	BURN-IN VERSION	933795510652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC154N3	N3	N3 Package version	935011790112	12/31/99	06/30/00	None Noted	2,4, M	No Volume, limited mfg capability
74HC161	N-B	BURN-IN VERSION	933795530652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC163	N-B	BURN-IN VERSION	933795540652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC165	N-B	BURN-IN VERSION	933795560652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC174	N-B	BURN-IN VERSION	933795570652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC20N/S15	N	Selection Type only	935073760112	12/31/99	06/30/00	Standard product	7	No Volume
74HC21	N-B	BURN-IN VERSION	933833330652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC243	N-B	BURN-IN VERSION	933795580652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC244	N-B	BURN-IN VERSION	933784570652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC244D/S15	D	Selection Type only	935150180118	12/31/99	06/30/00	Standard product	7	No Volume
74HC245	N-B	BURN-IN VERSION	933795590652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC251	N-B	BURN-IN VERSION	933795600652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC27	N-B	BURN-IN VERSION	933795460652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC283	N-B	BURN-IN VERSION	933840600652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC32	N-B	BURN-IN VERSION	933784590652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC32N/S15	N	Selection Type only	933785800112	12/31/99	06/30/00	Standard product	7	No Volume
74HC365	N-B	BURN-IN VERSION	933795610652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC390	N-B	BURN-IN VERSION	933795630652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC393	N-B	BURN-IN VERSION	933795640652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC4049	N-B	BURN-IN VERSION	933815630652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC4053D/S15	D	Selection Type only	935073750118	12/31/99	06/30/00	Standard product	7	No Volume
74HC4066	N-B	BURN-IN VERSION	933795680652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC4067N3	N3	N3 Package version	935011890112	12/31/99	06/30/00	None Noted	2,4, M	No Volume, limited mfg capability
74HC4514N3	N3	N3 Package version	935011910112	12/31/99	06/30/00	None Noted	2,4, S	No Volume, limited mfg capability
74HC4515N3	N3	N3 Package version	935011930112	12/31/99	06/30/00	None Noted	2,4, S	No Volume, limited mfg capability
74HC646N3	N3	N3 Package version	935011830112	12/31/99	06/30/00	None Noted	2,4, M	No Volume, limited mfg capability
74HC648N3	N3	N3 Package version	935011850112	12/31/99	06/30/00	None Noted	2,4, S	No Volume, limited mfg capability
74HC688	N-B	BURN-IN VERSION	933795660652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC7046A	N-B	BURN-IN VERSION	935043470112	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC73	N-B	BURN-IN VERSION	933776760652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HC74	N-B	BURN-IN VERSION	933795470652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT00	N-B	BURN-IN VERSION	933795700652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT02	N-B	BURN-IN VERSION	933776770652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT04	N-B	BURN-IN VERSION	933795710652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT04D/S15	D	Selection Type only	935058690118	12/31/99	06/30/00	Standard product	7	No Volume
74HCT08	N-B	BURN-IN VERSION	933795720652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT08N/S15	N	Selection Type only	935019330112	12/31/99	06/30/00	Standard product	7	No Volume

Exh C - Att: 3

PHILIPS PART NUMBER	PHILIPS PKG	PHILIPS PART DESCRIPTION	PHILIPS 12 NC NUMBER	LAST TIME BUY DATE	LAST TIME DLVY DATE	REPLACEMENT PART	STATUS CODE(S)	COMMENTS
74HCT10	N-B	BURN-IN VERSION	933926760652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT109	N-B	BURN-IN VERSION	933928470652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT11	N-B	BURN-IN VERSION	933979690652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT125	N-B	BURN-IN VERSION	933928450652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT125D/S15	D	Selection Type only	935058700118	12/31/99	06/30/00	Standard product	7	No Volume
74HCT126	N-B	BURN-IN VERSION	933969940652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT137	N-B	BURN-IN VERSION	933979680652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT138	N-B	BURN-IN VERSION	933829450652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT138D/S15	D	Selection Type only	935152260118	12/31/99	06/30/00	Standard product	7	No Volume
74HCT139	N-B	BURN-IN VERSION	933889770652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT14	N-B	BURN-IN VERSION	933969910652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT154N3	N3	N3 Package version	935011800112	12/31/99	06/30/00	None Noted	2,4, M	No Volume, limited mfg capability
74HCT157	N-B	BURN-IN VERSION	933928510652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT161	N-B	BURN-IN VERSION	933928480652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT173	N-B	BURN-IN VERSION	933969950652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT175	N-B	BURN-IN VERSION	933928490652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT20D/S15	D	Selection Type only	935153960118	12/31/99	06/30/00	Standard product	7	No Volume
74HCT21	N-B	BURN-IN VERSION	933969920652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT244	N-B	BURN-IN VERSION	933776780652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT245	N-B	BURN-IN VERSION	933776790652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT245D/S15	D	Selection Type only	935152270118	12/31/99	06/30/00	Standard product	7	No Volume
74HCT27	N-B	BURN-IN VERSION	933795730652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT280D/S15	D	Selection Type only	935153980118	12/31/99	06/30/00	Standard product	7	No Volume
74HCT30	N-B	BURN-IN VERSION	933969930652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT365	N-B	BURN-IN VERSION	933795760652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT367	N-B	BURN-IN VERSION	933969960652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT373	N-B	BURN-IN VERSION	933795770652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT393	N-B	BURN-IN VERSION	933795780652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT4059N3	N3	N3 Package version	935011880112	12/31/99	06/30/00	None Noted	2,4, M	No Volume, limited mfg capability
74HCT4067N3	N3	N3 Package version	935011900112	12/31/99	06/30/00	None Noted	2,4, M	No Volume, limited mfg capability
74HCT4514N3	N3	N3 Package version	935011910112	12/31/99	06/30/00	None Noted	2,4, S	No Volume, limited mfg capability
74HCT646N3	N3	N3 Package version	935011840112	12/31/99	06/30/00	None Noted	2,4, M	No Volume, limited mfg capability
74HCT74	N-B	BURN-IN VERSION	933795750652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT85	N-B	BURN-IN VERSION	933928500652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT86	N-B	BURN-IN VERSION	933928440652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
74HCT86D/S15	D	Selection Type only	935153970118	12/31/99	06/30/00	Standard product	7	No Volume
74HCU04	N-B	BURN-IN VERSION	933795400652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF4001UBP	N-B	BURN-IN VERSION	933636620652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF4007UBP	N-B	BURN-IN VERSION	933636650652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40097BP	N-B	BURN-IN VERSION	933636970652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40106BP	N-B	BURN-IN VERSION	933636660652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF4011UBP	N-B	BURN-IN VERSION	933636680652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40160BP	N-B	BURN-IN VERSION	933637010652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40161BP	N-B	BURN-IN VERSION	933637020652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40162BP	N-B	BURN-IN VERSION	933637030652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40174BP	N-B	BURN-IN VERSION	933637060652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume

Exh C - Att: 3

PHILIPS PART NUMBER	PHILIPS PKG	PHILIPS PART DESCRIPTION	PHILIPS 12 NC NUMBER	LAST TIME BUY DATE	LAST TIME DLVY DATE	REPLACEMENT PART	STATUS CODE(S)	COMMENTS
HEF40192BP	N-B	BURN-IN VERSION	933637100652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40193BP	N-B	BURN-IN VERSION	933637110652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40194BP	N-B	BURN-IN VERSION	933637120652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40195BP	N-B	BURN-IN VERSION	933637130652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40240BP	N-B	BURN-IN VERSION	933637640652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40244BP	N-B	BURN-IN VERSION	933637650652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40245BP	N-B	BURN-IN VERSION	933637660652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40373BP	N-B	BURN-IN VERSION	933637670652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF40374BP	N-B	BURN-IN VERSION	933637680652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF4069UBP	N-B	BURN-IN VERSION	933636790652	12/31/99	06/30/00	DIL / SO WITH NO BURN-IN OPTION	2, 6	No Volume
HEF4505BP	N	64-Bit, 1-bit Word RAM	933334280652	12/31/99	06/30/00	None Noted	2, S	No Volume, limited mfg capability