

Exh C - Att: 2

DN-42 RE-ACTIVATED PART TYPES

| PHILIPS TYPE NUMBER | PHILIPS NA PART NUMBER | PHILIPS 12 NC NUMBER | WITHDRAWAL DN NUMBER | RETENTION REASON | SPECIAL COMMENTS |
|---------------------|------------------------|----------------------|----------------------|---|---|
| CV3825N | CV3825 N | 935181790112 | 38 | Customer Request | Microcontroller |
| CV3836 B | CV3836 B | 935223100518 | 40 | Customer Request | Microcontroller |
| CV3836 B | CV3836 B | 935223100557 | 40 | Customer Request | Microcontroller |
| | | | | | |
| BAQ806 | | 934051250115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG50D | | 934031100115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG50D | | 934031100135 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG50G | | 934031110115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG50G | | 934031110135 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG50J | | 934031120115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG50J | | 934031120135 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG50K | | 934031930115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG50M | | 934031940115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG60D | | 934031130115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG60G | | 934031140115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG60G | | 934031140115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG60J | | 934031150115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG60J | | 934031150115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG60K | | 934031950115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG60M | | 934031960115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG60M | | 934031960115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG60M | | 934031960135 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG70D | | 934031160115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG70G | | 934031170115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG70J | | 934031180115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG80B | | 934033620115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG80D | | 934033640115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG80G | | 934033670115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BYG80J | | 934033680115 | DN40 | Customer requirement | Maintain complete 1.5A SMD range |
| BZG03-C10 | | 934028930115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C100 | | 934029180115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C11 | | 934028940115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C12 | | 934028950115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C15 | | 934028970115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C150 | | 934029220115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C18 | | 934028990115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C180 | | 934029240115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C200 | | 934029250115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C22 | | 934029010115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C24 | | 934029020115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C27 | | 934029030115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |

Exh C - Att: 2

| PHILIPS TYPE NUMBER | PHILIPS NA PART NUMBER | PHILIPS 12 NC NUMBER | WITHDRAWAL DN NUMBER | RETENTION REASON | SPECIAL COMMENTS |
|------------------------|---------------------------|-------------------------|-------------------------|---|---|
| BZG03-C33 | | 934029050115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C36 | | 934029060115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C39 | | 934029070115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C43 | | 934029080115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C62 | | 934029120115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG03-C75 | | 934029140115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG04-15 | | 934033820115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZG04-47 | | 934033940115 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| BZD23-C36 | | 933753520113 | DN40 | Customer requirement for small reels (1.5K) | Larger reel size is 7.5K (12NC End 135) |
| PBYR1080 | | 934020560127 | DN40 | Customer requirement | |

| | | | | | |
|--------------|--|--------------|------|-----------------|------------------------|
| PCF2100CT/F1 | | 935195690112 | DN41 | Customer demand | Replaces non-C version |
| PCF2100CT/F1 | | 935195690118 | DN41 | Customer demand | Replaces non-C version |
| PCF2112CP/F1 | | 935195740112 | DN41 | Customer demand | Replaces non-C version |
| PCF2112CT/F1 | | 935195750112 | DN41 | Customer demand | Replaces non-C version |
| PCF2112CT/F1 | | 935195750118 | DN41 | Customer demand | Replaces non-C version |

| | | | | | |
|------------|------------|--------------|------|--|-----------------------------------|
| 74HCt9115D | 74HCt9115D | 933987870112 | DN40 | Dramatic increase in business activity | Designed into an Automotive appl. |
| 74HCt9115D | 74HCt9115D | 933987870118 | DN40 | Dramatic increase in business activity | Designed into an Automotive appl. |
| 74HCT9115N | 74HCT9115N | 933987860112 | DN40 | Dramatic increase in business activity | Designed into an Automotive appl. |
| 74HCT9115U | 74HCT9115U | 933987880005 | DN40 | Dramatic increase in business activity | Designed into an Automotive appl. |
| 74HC9115D | 74HC9115D | 933987840112 | DN40 | Dramatic increase in business activity | Designed into an Automotive appl. |
| 74HC9115D | 74HC9115D | 933987840118 | DN40 | Dramatic increase in business activity | Designed into an Automotive appl. |
| 74HC9115N | 74HC9115N | 933987830112 | DN40 | Dramatic increase in business activity | Designed into an Automotive appl. |
| 74HC9115U | 74HC9115U | 933987850005 | DN40 | Dramatic increase in business activity | Designed into an Automotive appl. |
| | | | | | |