




## *Information Brief*



### Versatile RF Front End Building Blocks Enable Cost-Effective Solutions from DC to 2.4 GHz

*Can also contribute to extended battery life*

This new family of RF building blocks consists of the MC13142, MC13143 and MC13144. All three ICs are designed using Motorola's MOSAIC V™ high frequency bipolar wafer process to provide excellent performance in both analog and digital communication systems.

The MC13142 provides a general purpose solution for RF front ends because it contains all of the basic functions needed. The MC13143 and MC13144 combine to provide a higher performance solution for RF front ends. The system partitioning between the MC13143 and 13144 provides *improved isolation, more versatility, and simplifies the interface* with external devices such as filters and other active components.

The MC13142 is a *complete* RF front end with a first amplifier, voltage controlled oscillator (VCO), and a downconverter. This device is suitable for use in a wide variety of RF applications, and features wideband operation, low noise, high gain and high linearity, while maintaining low power consumption. The wide IF bandwidth of the mixer (DC to 1.8 GHz) allows the MC13142 to also be used as an upconverter and exciter amplifier.

The MC13143 is a high compression linear mixer with a single-ended RF input, differential IF output, and differential local oscillator (LO) inputs, which consumes as little as 1.8 mW. This mixer is designed for up or down conversion anywhere from DC to 2.4 GHz.

The MC13144 is a low noise amplifier (LNA) with programmable bias. The device includes a cascode LNA that is usable at up to 2.0 GHz with a 1.8 Vdc supply. This IC incorporates a two-bit digital programming capability of the LNA bias, which allows the user to optimize the noise figure (NF) and the gain associated with the NF.

The MC13142 *or* the MC13143 and MC13144 together can be easily combined with the MC13158 Wideband FM IF for data radios or other FM applications.

## FEATURES

### MC13142 DC to 1.8 GHz LNA, Mixer and VCO

- Complete RF front end
- Low power consumption of 13 mA with a  $V_{CC}$  of 2.7 to 6.5 V
- Linearity adjustment increases the amplifier third order intercept ( $IP_{3in}$ ) up to 20 dBm
- High mixer linearity ( $P_{i1.0dB}$ ) of 3.0 dBm
- Single-ended 50 $\Omega$  input, double balanced mixer
- Wide RF, LO, and IF bandwidths of DC to 1.8 GHz

### MC13143 DC to 2.4 GHz Linear Mixer

- Ultra low power consumption of 1.0 mA with a  $V_{CC}$  of 1.8 to 6.5 V
- Linearity adjustment of up to 20 dBm for  $IP_{3in}$
- High mixer linearity ( $P_{i1.0dB}$ ) of 3.0 dBm
- Single-ended 50 $\Omega$  input, double balanced mixer
- Wide input, LO, and output bandwidths of DC to 2.4 GHz
- Can be used as an up or down mixer, or in a direct conversion solution.

### MC13144 VHF to 2.0 GHz LNA with Programmable Bias

- Low power supply voltage of 1.8 to 6.0 V
- Programmable bias optimizes NF and the gain associated with NF
- Gain of 17 dB at 900 MHz
- Noise figure of 1.4 dB at 900 MHz
- 1.0 dB compression point of -7.0 dB

## TYPES OF APPLICATIONS

- Any 900 MHz ISM band applications such as:
  - Active RF tags
  - Video or data link security systems
  - Consumer or industrial remote control
  - Remote keyless entry
  - TV video links
  - High fidelity audio links
  - Wireless telephone headsets

**TYPES OF APPLICATIONS (CONTINUED)**

- UHF Family Radio Services
- UHF and 800 MHz Special Mobile Radio
- 800 MHz cellular phones
- GSM, PCS, DECT and PHS handsets at 1.8 to 2.0 GHz
- Cordless phones in the 902 to 928 MHz band
- High power spread spectrum and low power data links in the 900 MHz ISM band
- Wideband data links

**BENEFITS TO YOU**

- Lowers system cost and manufacturing costs by reducing component count and circuit complexity over other solutions.
- Can be used in two-cell battery-powered applications with a power supply voltage as low as 1.8 V (MC13143/144).
- Improved battery life due to low power consumption, and standby mode when receiver is not in use.
- Provides system design flexibility with one-chip (MC13142) or two-chip (MC13143/144) RF front end solutions.
- Higher circuit and system density with small surface mount packages.
- Flexibility in receiver system partitioning because the differential open collector mixer outputs of the MC13142 and MC13143 simplify the interface to filters and back-end IF devices, such as the MC13158.
- Improved reliability due to lower power dissipation.
- Smaller battery for portable applications with 1.8 to 2.7 V operation.
- Optimized mixer loading for improved linearity with single-ended 50Ω double balanced mixer design.

**A SOLUTION FOR THESE QUESTIONS**

- Are you designing a wireless communications system that operates in the 900 MHz ISM or 1.8 to 2.0 GHz frequency range?
- Is reduced space or small printed circuit board size a critical design requirement?
- Do you want to reduce your system cost with a more cost-effective design requiring fewer external components?



Freescale Semiconductor, Inc.  
 ARCHIVED BY FREESCALE SEMICONDUCTOR, INC. 2005

**A SOLUTION FOR THESE QUESTIONS (CONTINUED)**


- Do you need to decrease the battery size and improve the battery life in your wireless system by reducing the operating voltage and power consumption?
- Does your application require an optimized noise figure for your LNA?
- Do you want a complete general purpose RF front end in a single IC?
- Do you need to optimize your mixer loading to improve system linearity?

**LITERATURE**

Complete data sheets containing full specifications, characteristic curves, circuit configurations, applications information, and sample printed circuit board layouts are available through Motorola's LDC as MC13142/D, MC13143/D and MC13144/D. Alternately, call Mfax at 602/244-6609 and key-in MC13142, MC13143 and/or MC13144.

**ORDERING INFORMATION**

Device	Operating Temperature Range	Package
MC13142D	T <sub>A</sub> = -40°C to +85°C	SO-16
MC13143D		SO-8
MC13144D		SO-8

Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters can and do vary in different applications. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights nor the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part. Motorola and  are registered trademarks of Motorola, Inc. Motorola, Inc. is an Equal Opportunity/Affirmative Action Employer.

**How to reach us:**

**USA/EUROPE/Locations Unlisted:** Motorola Literature Distribution;  
 P.O. Box 5405; Denver, CO. 80217 or call 1-800-441-2447

**JAPAN:** Nippon Motorola Ltd.: SPD, Strategic Planning Office 4-32-1,  
 Nishi-Gotanda, Shinagawa-ku, Tokyo 141, Japan. 81-3-5487-8488

**Customer Focus Center:** 1-800-521-6274

**ASIA/PACIFIC:** Motorola Semiconductors H.K. Ltd.;  
 8B Tai Ping Industrial Park, 51 Ting Kok Road, Tai Po, N.T.,  
 Hong Kong. 852-26629298

**Mfax™:** RMFAX0@email.sps.mot.com – TOUCHTONE 1-602-244-6609  
 Motorola Fax Back System US & Canada Only 1-800-774-1848  
<http://sps.motorola.com/mfax/>

Mfax is a trademark of Motorola, Inc.

Home Page: <http://motorola.com/sps/>  
 Wireless Page: [motorola.com/wireless-semi](http://motorola.com/wireless-semi)