

i.MX 8 FAMILY OF APPLICATIONS PROCESSORS

Built with advanced media processing, secure domain partitioning and innovative vision processing, the i.MX 8 applications processor family can drive multiple display automotive applications, industrial systems, vision, HMI and single-board computers.

TARGET APPLICATIONS

- Automotive infotainment—instrument cluster, head unit, heads-up display (HUD), rear seat entertainment and full digital electronic cockpit (eCockpit)
- Advanced industrial human machine interface (HMI) and control
- Single-board computers
- Home/Building

MULTIPLE SYSTEMS, ONE PROCESSOR

- **Easily combine multiple systems into one**
Build multiple platforms with multiple operating systems on a single i.MX 8 processor. The i.MX 8 full-chip hardware-based virtualization, system MMU, resource partitioning and split GPU and display architecture help enable faster time-to-market and lower cost than simple hypervisor techniques alone.
- **Secure Your System with SECO HSM**
Exceptional security via the SECO (security controller) with an isolated, dedicated hardware security module (HSM) protects the system and its connections.
- **Isolate key systems with on-chip hardware firewalls**
Isolate critical services such as over-the-air (OTA) upgrades by running within 16 separate run-time programmable hardware firewall domains.
- **Improve your system reliability with FDSOI**
Built using 28nm FDSOI, the i.MX 8 applications processor enables improved MTBF and decreases soft error rates due to FDSOI's inherently high immunity to alpha particle flux.



THE NEW USER INTERACTION PARADIGM

- **Create advanced vision-based HMI systems**
High-performance end-to-end vision processing helps enable vision-based assistance, tracking and object detection.
- **360-degree expanded sight**
Utilize multi-camera input, digital stitching and VX vision extensions and provide a view from any angle.
- **Multi-domain voice recognition**
Utilize the Arm® Cortex®-A72, Cortex A53 and Cortex-M4F cores as well as the HiFi 4 DSP* for advanced echo cancellation, key word detection and speech recognition for hands-off interaction.

MULTI-DISPLAY & MULTI-DOMAIN FUNCTIONALITY

- **Four screens of independent content**
Develop innovative, multi-screen platforms through the ability to drive up to four 1080p screens with independent content, or a single 4K screen.

• Help your display stay up and correct

SafeAssure® ASIL B-ready hardware protects critical visual information with fail-over-capable quality of service to any display.

• Offload time-critical tasks

Utilize dual Cortex-M4F cores for time-critical tasks such as backup camera display, audio control and general system monitoring and wakeup.

THE SCALABLE PLATFORM OF CHOICE

• Comprehensive software support

Android™*, Linux®*, QNX, Green Hills®, DornerWorks XEN and FreeRTOS™

• Automotive & Industrial qualified

Automotive: -40 °C to 125 °C Tj
Industrial: -40 °C to 105 °C Tj

PIN AND POWER COMPATIBLE

Highly scalable design options allow a single platform to cover multiple products. Pin- and power-compatible package (in 0.75 pitch) allow a single PCB platform and utilize different i.MX 8 processors as product needs dictate.*

EARLY DEVELOPMENT ACCESS

The i.MX 8 multi-sensory evaluation kit (MEK) is available now to prototype i.MX 8 systems. Contact your NXP sales representative for details.

i.MX 8 FAMILY—DIFFERENTIATED FEATURES

Feature	i.MX 8QuadMax	i.MX 8QuadPlus
Arm® Core	2 x Arm Cortex®-A72	1 x Cortex-A72
Arm Core	4 x Cortex-A53	4 x Cortex-A53
Arm Core	2 x Cortex-M4F	2 x Cortex-M4F
DSP Core	HiFi 4 DSP	HiFi 4 DSP
GPU	2 x GC7000XSVX	2 x GC7000XSVX
PCIe 3.0	1 x PCIe (2-lane)*	1 x PCIe (1-lane)


*2-lane PCIe can act as 2 x 1-lane PCIe

i.MX 8 FAMILY—COMMON FEATURES

Feature	Description	Feature	Description
DRAM	64-bit LPDDR4	QuadSPI	2 x QuadSPI (1 x OctoSPI)
VPU	4k h.265 decode, h.264 (1080p60) decode and encode	USB with PHY	1 x USB 3.0, 2 x USB 2.0
Display controller	2 x DCs with WARP and failover	SPDIF Tx/Rx	1 x
MIPI DSI	2 x 4-lane MIPI DSI	SD and eMMC	3 x SD 3.0/eMMC 5.0
MIPI CSI	2 x 4-lane MIPI CSI	NAND	1 x – BCH62
LVDS	2 x LVDS	FPGA Interface	Yes – 4 x data lane, 1 x Clock
HDMI, eDP, DP Tx	1 x HDMI 2.0a/eDP 1.4/DP 1.3 HDCP 2.2	I²C	5 x I²C (high speed) + 8 x I²C (low speed)
HDMI Rx	1 x HDMI 1.4 Rx HDCP 2.2	SPI	4 x SPI
SATA 3.0	1 x SATA 3.0 (1-lane) or PCIe® (1-lane)*	Audio Interfaces	2 x ESAI, 5 x I²S/SAI
Security	SECO Hardware Security Module (HSM), Flashless SHE, Inline DDR encryption, Hardware Domain Firewalls	Keypad	1 x
CAN	3 x CAN FD	MPEG-2 T/S	2 x MPEG-2 T/S
Ethernet	2 x Gigabit Ethernet with AVB	UART	5 x UART 1 x UART per Arm® Cortex®-M4F

*The SATA 3.0 controller can be used as PCIe (1-lane). This is in addition to the other PCIe controllers. Note: Accessing muxable controller's full capabilities is dependent upon board component choices.

i.MX 8 FAMILY BLOCK DIAGRAM



Note: Accessing muxable controller's full capabilities is dependent upon board component choices.

Available on certain product families

www.nxp.com/iMX8

NXP, the NXP logo and SafeAssure are trademarks of NXP B.V. All other product or service names are the property of their respective owners. Vulkan is a registered trademark of the Khronos Group Inc. Arm, Cortex and TrustZone are trademarks or registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. ©2019–2021 NXP B.V.